

Multi-Clamp Vacuum Pump VC-M-PU

Suction rate of 4.1 m³/h



Suitability for Industry Specific Applications



Applications

- Portable vacuum pump for use in combination with the Schmalz Multi-Clamp
- Thanks to its compact and solid design and its power, the pump is suitable for a multitude of additional applications
- Plug-and-play solution thanks to vacuum connection via quick-connect coupling and AC power supply

Multi-Clamp Vacuum Pump VC-M-PU

Design

- Dry-running, oil-free vacuum pump
- Ready-to-connect design with quick-connect coupling (ND 5 mm) and AC plug
- Integrated easy-to-clean filter

Product highlights

- Powerful, dry-running vacuum pump suitable for a variety of applications
- Integrated manometer enables quick reading of the vacuum level
- Integrated cable drum avoids loose cables hanging around
- Ergonomic design optimized for mobile use on the construction site

Designation Code Multi-Clamp Vacuum Pump VC-M-PU

VC-M-PU	–	4	–	110V-AC
1		2		3

1 – Abbreviated designation

Code	Type
VC-M-PU	Multi-Clamp vacuum pump

2 – Performance class

Code	Suction capacity in m ³ /h
4	4

3 – Supply voltage

Code	Type
110V-AC	110 Volt single-phase
230V-AC	230 Volt single-phase

The Multi-Clamp vacuum pump is delivered assembled. The product consists of:

- Dry-running vacuum pump
- Housing with integrated cable drum and vacuum manometer

Available accessories: foot interrupter, accessory set for operation of two VC-M-V with one pump

Ordering Data Multi-Clamp Vacuum Pump VC-M-PU

Type	Part no.
VC-M-PU 4 110V-AC	10.01.12.02051
VC-M-PU 4 230V-AC	10.01.12.02040

Multi-Clamp Vacuum Pump VC-M-PU

Suction rate of 4.1 m³/h

Ordering Data Accessories Multi-Clamp Vacuum Pump VC-M-PU

Type			Part no.
Accessories	Operation of two VC-M-V with one pump	ZUB VC-M-V	10.01.12.02054
Foot-operated interrupter	with catch	FU 5 3/2 R	10.01.12.03036


Technical Data Multi-Clamp Vacuum Pump VC-M-PU

Type	Rated power 50 Hz [kW]	Rated power 60 Hz [kW]	Protection type IP	Suction rate (50 Hz) [m ³ /h]	Suction rate (60 Hz) [m ³ /h]	Voltage 50 Hz	Voltage 60 Hz	Weight [kg]
VC-M-PU 4 110V-AC	0.18	0.22	IP 54	-	-	-	110V-AC	8.5
VC-M-PU 4 230V-AC	0.18	0.22	IP 54	4.1	-	230V-AC	-	8.5

Multi-Clamp Vacuum Pump VC-M-PU

Suction rate of 4.1 m³/h

Design Data Multi-Clamp Vacuum Pump VC-M-PU



VC-M-PU 4

Multi-Clamp Vacuum Pump VC-M-PU

Suction rate of 4.1 m³/h

Design Data Multi-Clamp Vacuum Pump VC-M-PU

Type	B [mm]	B1 [mm]	G2	H [mm]	L [mm]	L1 [mm]
VC-M-PU 4 110V-AC	134	161	G1/4"-M	236	255	269
VC-M-PU 4 230V-AC	134	161	G1/4"-M	236	255	269