

# Hose Clamps SSB / SSD

Clamping range from 10 mm to 90 mm



## Suitability for Industry Specific Applications

### Applications

- Hose clamp SSB for securing smooth hoses
- Hose clamp SSD for securing hoses with wire reinforcement



Hose Clamps SSB / SSD

### Design

- Hose clamp made of galvanized steel
- Stable threaded spindle for safe clamping

### Product Highlights

- Clamps up to clear diameter 84 mm suitable for all offered hoses
- Secure hold for all vacuum hoses thanks to stable threaded spindle, also with wire spiral

### Designation Code Hose Clamps SSB / SSD

<b>SSB</b>	-	<b>10-16</b>	-	<b>ST-VZ</b>
1		2		3

#### 1 – Abbreviated designation

Code	Version
SSB	Smooth hoses
SSD	Hoses with wire reinforcement

#### 2 – Clamping range

Code	Clamping range in mm
10-16...85-90	ø 10-16 to 85-90

#### 3 – Material

Code	Material
ST-VZ	Steel, plated
A2	Stainless steel

Hose clamp SSB / SSD is delivered in the desired diameter.

Available accessories: cap

## Hose Clamps SSB / SSD

Clamping range from 10 mm to 90 mm

### Ordering Data Hose Clamps SSB / SSD

Type	Part no.	Accessories	Part no.
SSB 8-12 ST-VZ	10.07.10.00158	-	-
SSB 10-16 ST-VZ	10.07.10.00001	Cap (rectangular)	20.12.01.00036
SSB 12-20 ST-VZ	10.07.10.00159	-	-
SSB 12-22 ST-VZ	10.07.10.00160	-	-
SSB 16-27 ST-VZ	10.07.10.00002	Cap (rectangular)	20.12.01.00036
SSB 20-32 ST-VZ	10.07.10.00003	Cap (rectangular)	20.12.01.00036
SSB 23-35 ST-VZ	10.07.10.00161	-	-
SSB 32-50 ST-VZ	10.07.10.00004	Cap (rectangular)	20.12.01.00036
SSB 40-60 ST-VZ	10.07.10.00005	Cap (rectangular)	20.12.01.00036
SSB 60-80 ST-VZ	10.07.10.00006	Cap (rectangular)	20.12.01.00036
SSD 24-27 ST-VZ	10.07.10.00086	-	-
SSD 28-32 ST-VZ	10.07.10.00087	-	-
SSD 35-40 ST-VZ	10.07.10.00018	-	-
SSD 37-42 ST-VZ	10.07.10.00019	-	-
SSD 42-46 ST-VZ	10.07.10.00156	-	-
SSD 43-48 ST-VZ	10.07.10.00020	-	-
SSD 45-50 ST-VZ	10.07.10.00157	-	-
SSD 57-62 ST-VZ	10.07.10.00036	-	-
SSD 60-68 ST-VZ	10.07.10.00017	-	-
SSD 65-70 ST-VZ	10.07.10.00098	-	-
SSD 76.5-84 ST-VZ	10.07.10.00037	-	-
SSD 80-85 ST-VZ	10.07.10.00136	-	-
SSD 85-90 ST-VZ	10.07.10.00102	-	-

### Technical Data Hose Clamps SSB / SSD

Type	Clamping range [mm]
SSB 10-16 ST-VZ	10.0 ... 16.0 mm
SSB 12-20 ST-VZ	12.0 ... 20.0 mm
SSB 12-22 ST-VZ	12.0 ... 22.0 mm
SSB 16-27 ST-VZ	16.0 ... 27.0 mm
SSB 20-32 ST-VZ	20.0 ... 32.0 mm
SSB 23-35 ST-VZ	23.0 ... 35.0 mm
SSB 32-50 ST-VZ	32.0 ... 50.0 mm
SSB 40-60 ST-VZ	40.0 ... 60.0 mm
SSB 60-80 ST-VZ	60.0 ... 80.0 mm
SSB 8-12 ST-VZ	8.0 ... 12.0 mm
SSD 24-27 ST-VZ	24.0 ... 27.0 mm
SSD 28-32 ST-VZ	28.0 ... 32.0 mm
SSD 35-40 ST-VZ	35.0 ... 40.0 mm
SSD 37-42 ST-VZ	37.0 ... 42.0 mm
SSD 42-46 ST-VZ	42.0 ... 46.0 mm
SSD 43-48 ST-VZ	43.0 ... 48.0 mm
SSD 45-50 ST-VZ	45.0 ... 50.0 mm
SSD 57-62 ST-VZ	57.0 ... 62.0 mm
SSD 60-68 ST-VZ	60.0 ... 68.0 mm
SSD 65-70 ST-VZ	65.0 ... 70.0 mm
SSD 76.5-84 ST-VZ	76.5 ... 84.0 mm
SSD 80-85 ST-VZ	80.0 ... 85.0 mm
SSD 85-90 ST-VZ	85.0 ... 90.0 mm

## Hose Clamps SSB / SSD

Clamping range from 10 mm to 90 mm

### Design Data Hose Clamps SSB / SSD

Type	d1 [mm]	d2 [mm]	L [mm]
SSB 8-12 ST-VZ	8	12	9
SSB 10-16 ST-VZ	10	16	9
SSB 12-20 ST-VZ	12	20	9
SSB 12-22 ST-VZ	12	22	9
SSB 16-27 ST-VZ	16	27	9
SSB 20-32 ST-VZ	20	32	9
SSB 23-35 ST-VZ	23	35	9
SSB 32-50 ST-VZ	32	50	9
SSB 40-60 ST-VZ	40	60	9
SSB 60-80 ST-VZ	60	80	9
SSD 24-27 ST-VZ	24	27	12
SSD 28-32 ST-VZ	28	32	12
SSD 35-40 ST-VZ	35	40	13
SSD 37-42 ST-VZ	37	42	13
SSD 42-46 ST-VZ	42	46	18
SSD 43-48 ST-VZ	43	48	15
SSD 45-50 ST-VZ	45	50	18
SSD 57-62 ST-VZ	57	62	15
SSD 60-68 ST-VZ	60	68	15
SSD 65-70 ST-VZ	65	70	13
SSD 76.5-84 ST-VZ	77	84	18
SSD 80-85 ST-VZ	80	85	19
SSD 85-90 ST-VZ	85	90	19