

Protection Covers PC

Diameter (Ø) from 125 mm to 400 mm



Protection Covers PC

Design

- Robust and tear-resistant material, resistant to external environmental influences
- Slid over suction cups / suction plates and fastened with the integrated elastic band
- Diameters of the covers are designed to match the corresponding diameter ranges of the suction cups and suction plates

Designation code Protection Covers PC

PC	–	125
1		2

1 – Abbreviated designation

Code	Version
PC	PC

Protection cover PC is delivered with the desired diameter.

Suitability for industry specific applications

Application

- High quality protection cover for suction plates during storage or when not in use
- Protection against pollution (dust or moisture) and aging (by ozone or UV impact) in outdoor areas
- Use in combination with suction plates and suction cups such as SPU and SGF
- Use with manual glass lifting devices indoors and outdoors during storage and transport

Product highlights

- High quality coating protects against contamination, aging and deformation of the sealing lip during storage
- Quick and easy installation thanks to integrated rubber band; reusable
- Large range of diameters optimized for flat and bellows suction cups and suction plates

2 – Diameter

Code	Diameter in mm
125...400	Ø 125 to 400

Protection Covers PC

Diameter (Ø) from 125 mm to 400 mm

Ordering data Protection Covers PC

Type	Part no.
PC 125	10.01.01.13086
PC 150	10.01.01.13087
PC 175	10.01.01.13088
PC 200	10.01.01.13089
PC 250	10.01.01.13090
PC 300	10.01.01.13091
PC 350	10.01.01.13092
PC 400	10.01.01.13093

Technical data Protection Covers PC


Type*	Clamping range [mm]
PC 125	110.0 ... 135.0 mm
PC 150	135.0 ... 165.0 mm
PC 175	165.0 ... 190.0 mm
PC 200	190.0 ... 220.0 mm
PC 250	220.0 ... 275.0 mm
PC 300	275.0 ... 325.0 mm
PC 350	325.0 ... 375.0 mm
PC 400	375.0 ... 425.0 mm

*Suction cup protection covers PC are designed for the use with suction cups and suction plates that are out of use. They cannot be used during handling.

Protection Covers PC

Diameter (\varnothing) from 125 mm to 400 mm

Design data Protection Covers PC



PC 125 - 400

Protection Covers PC

Diameter (Ø) from 125 mm to 400 mm

Design data Protection Covers PC

Type	D [mm]	d2 [mm]
PC 125	125	65
PC 150	150	75
PC 175	175	90
PC 200	200	100
PC 250	250	125
PC 300	300	150
PC 350	350	175
PC 400	400	200