Accessories Needle Grippers SNG-AP





Accessories Needle Grippers SNG-AP

Design

- HTS holder system: Bolts with slot Ø 19 mm or ball Ø 28.5 mm
- Mounting plate: 38x15x11.5 mm, G1/4" female thread
- Sensor set for both end positions with M12 plug connectorPlug-in screw union in swiveling angular design for 6 mm
- Plug-in screw union in swiveling angular design for 6 mm hose diameter

Suitability for Industry Specific Applications

Applications

• For connecting needle grippers to the gripper system and to the media supply.

Product Highlights

- Universally applicable, since tooling connection is possible on different sides of the gripper
- Fast, reliable adaptation to a wide variety of workpieces thanks to standardized connection options
- Retrofittable sensor transmits status information (needles extended or retracted) to control system