

Non-Return Valves RSV

Nominal diameter from 6 mm to 54 mm



Suitability for Industry Specific Applications

Applications

- Non-return valve for maintaining the vacuum in the case of a power failure or a failure of the vacuum generator
- Can also be used with energy saving systems when handling non-porous materials
- May be installed in any orientation



Non-Return Valves RSV

Design

- Spring loaded seat valve
- Brass body (RSV 6, which is made of aluminum)
- Seat made of synthetic rubber, gasket made of nylon
- Stainless steel spring

Our Highlights...


- Seat type non-return valve
- Wide range of nominal diameters
- Very small size

Your Benefits...

- Closure of the vacuum line in order to maintain the system vacuum in the case, for example, of a power failure
- Very low to very high nominal flow rates possible
- Also suitable for use in restricted spaces



Designation Code Non-Return Valves RSV



1 - Abbreviated designation

Code	Version
RSV	RSV

2 - Nozzle size

Code	Nozzle size in mm
6...54	6 to 54

3 - Connection

Code	Connection
G1/4-IG	G1/4-IG (IG = female (F))
G3/8-IG	G3/8-IG
G1/2-IG	G1/2-IG
G3/4-IG	G3/4-IG
G1-IG	G1-IG
G1-1/4-IG	G1-1/4-IG
G1-1/2-IG	G1-1/2-IG
G2-IG	G2-IG

Non-return valve RSV is delivered as a ready-to-connect product.



Schmalz - The Company
Vacuum Suction Cups
Special Grippers
Gripping Systems
Clamping Systems
Mounting Elements
Vacuum Generators
Valve Technology
Switches and Monitoring
Filters and Connections
Services
Contact
Glossary
Index of Products

Non-Return Valves RSV

Nominal diameter from 6 mm to 54 mm



Ordering Data Non-Return Valves RSV

Type	Part no.
RSV 6 G1/4-IG	10.05.05.00116
RSV 14 G3/8-IG	10.05.05.00002
RSV 18 G1/2-IG	10.05.05.00003
RSV 20 G3/4-IG	10.05.05.00004
RSV 28 G1-IG	10.05.05.00005
RSV 36 G1-1/4-IG	10.05.05.00006
RSV 42 G1-1/2-IG	10.05.05.00007
RSV 54 G2-IG	10.05.05.00008





Technical Data Non-Return Valves RSV

Type	Nominal size [mm]	Nominal flow rate [m³/h]	Nominal flow rate [l/min]	Opening pressure [mbar]	Operating temperature [°C]	Weight [kg]
RSV 6 G1/4-IG	6	5	84	200	-10 ... 70	0.04
RSV 14 G3/8-IG	14	20	334	20	-20 ... 100	0.18
RSV 18 G1/2-IG	18	26	434	20	-20 ... 100	0.19
RSV 20 G3/4-IG	20	45	750	20	-20 ... 100	0.27
RSV 28 G1-IG	28	75	1,250	20	-20 ... 100	0.49
RSV 36 G1-1/4-IG	36	125	2,084	20	-20 ... 100	0.74
RSV 42 G1-1/2-IG	42	200	3,334	20	-20 ... 100	0.98
RSV 54 G2-IG	54	350	5,834	20	-20 ... 100	1.11



Design Data Non-Return Valves RSV



RSV 6

RSV 14 - 54

Type	D [mm]	G1	G2	L [mm]	SW1 [mm]
RSV 6 G1/4-IG	-	G1/4"-F	G1/4"-F	43	16
RSV 14 G3/8-IG	34	G3/8"-F	G3/8"-F	59	23
RSV 18 G1/2-IG	34	G1/2"-F	G1/2"-F	62	27
RSV 20 G3/4-IG	41	G3/4"-F	G3/4"-F	69	33
RSV 28 G1-IG	52	G1"-F	G1"-F	84	40
RSV 36 G1-1/4-IG	63	G1-1/4"-F	G1-1/4"-F	88	50
RSV 42 G1-1/2-IG	71	G1-1/2"-F	G1-1/2"-F	96	50
RSV 54 G2-IG	87	G2"-F	G2"-F	100	70



Schmalz – The Company
Vacuum Suction Cups
Special Grippers
Gripping Systems
Clamping Systems
Mounting Elements
Vacuum Generators
Valve Technology
Switches and Monitoring
Filters and Connections
Services
Contact
Glossary
Index of Products