

Rotary Unions DEF

Max. rotation speed 3,500/min



Suitability for industry specific applications

Application

- Supplying fast-moving machine parts or rotating gripper systems with compressed air or vacuum



Rotary Unions DEF

Design

- Rotary union with steel rotor and body made of high-strength aluminum

Product highlights

- Rotary union for the supply of vacuum and compressed air, also for fast moving machine elements or grippers
- Durable, maintenance free design in high strength aluminium and steel

Designation code Rotary Unions DEF

DEF	–	R	–	3500
1		2		3

1 – Abbreviated designation

Code	Version
DEF	DEF

2 – Shape

Code	Type
GE	Straight
L	Left-hand thread
R	Right-hand thread
W	Angled

3 – Max. rotation speed

Code	Max. rotation speed per minute
21...3500	21 to 3,500

VACU-ZUF	–	DEF	–	60
1		2		3

1 – Abbreviated designation

Code	Version
VACU-ZUF	VACU-ZUF

2 – Shape

Code	Type
DEF	Rotary union

3 – Outside diameter

Code	Diameter in mm
60...100	Ø 60 to 100

The rotary union DEF / VACU-ZUF is delivered as a ready-to-connect product.