

# Vacuum Centers VZ

Suction rate from 4 m<sup>3</sup>/h to 165 m<sup>3</sup>/h



## Suitability for Industry Specific Applications

### Applications

- Vacuum center for use wherever there is a demand for high performance, safety and reliability



Vacuum Centers VZ

### Design

- Vacuum center, consisting of vacuum pump, vacuum reservoir, safety non-return valve, filter and manometer
- Motor protection switch and vacuum regulated motor switch (adjustable) available as options
- Coating RAL 7035

### Product Highlights

- Complete solution with pump, reservoir, manometer, filter and control (optional)
- Dry-running pump or oil-lubricated version for vibration-free operation and continuous output
- Vacuum reservoir secures workpiece in case of leakage or power failure
- Automatic energy saving function (optional) enables cost-saving continuous operation

### Designation Code Vacuum Centers VZ

VZ	-	TR	-	40	-	AC3	-	50	-	GMS
1		2		3		4		5		6

#### 1 – Abbreviated designation

Code	Version
VZ	VZ

#### 2 – Pump type

Code	Type
OG	Oil-lubricated
TR	Dry-running

#### 3 – Performance class

Code	Suction rate in m <sup>3</sup> /h
4...165	4 to 165

#### 4 – Supply voltage

Code	Type
AC	Single-phase
AC3	Three-phase

#### 5 – Reservoir volume

Code	Volume in l
5...200	5 to 200

#### 6 – Product addition

Code	Type
MS	Motor protection switch
GMS	Vacuum regulated motor protection switch

Vacuum centre VZ is delivered as a ready to connect product.

Available spare parts: replacement cartridge for air cleaner, replacement cartridge for oil filter

Vacuum Centers



## Vacuum Centers VZ

Suction rate from 4 m<sup>3</sup>/h to 165 m<sup>3</sup>/h

Available accessories: filter cartridge for vacuum reservoir